

## EV-803 Digital SD T.E.N.S



EV-803(C) is a Digital SD TENS with 5 modes: B(Burst), N(Normal), M(Pulse Rate Modulation), S1(Pulse Width Modulation) and S2(Pulse Rate Modulation). Pulse rate, pulse duration and modes are selected by press buttons. A compliance meter allowing the physical therapist to check the accumulated treatment time. A timer of 15, 30 and 60 minutes and a protection cap on the top of unit is available by order.

**Cannel:** Dual, isolated between channels

**Pulse Amplitude:** 0-80mA peak to peak into 500 ohm load.

**Pulse Rate:** Adjustable, from 1Hz ~ 150 Hz, 1 Hz/step

**Pulse Width:** Adjustable, from 30  $\mu$ s ~ 260  $\mu$ s, 10  $\mu$ s/step

**Mode:** B, N, M, S1, S2

**Wave Form:** Asymmetrical Bi-Phasic Square Pulse

**Voltage:** 0-40 V peak into 500 ohm load

**Size:** 100(H)X 60(W) X 21(T) mm

**\*A timer of 15, 30, 60 minutes is available by order.**